

**HUBBELL**  
Wiring Device-Kellems

**Heavy Duty Products, Single Pole  
Devices, Industrial Grade, Male,  
Receptacle, 300/400A 600V  
AC/DC, Single Conductor, Set  
Screw, Black**

By Hubbell Wiring Device-Kellems  
Catalog # [HBLMRBK](#)

Heavy Duty Products, Single Pole Devices, Industrial Grade, Male,  
Receptacle, 300/400A 600V AC/DC, Single Conductor, Set  
Screw, Black



## Features

- Industrial Grade
- Male
- Receptacle

## Application

High Ampacity Connections

## Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Environmental - Flammability - HB per UL94 or CSA 22.2. 0.17
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #4 to 4/0 AWG

## General

|                              |   |
|------------------------------|---|
| Catalog Number               | HBLMRBK   |
| Color                        | Black   |
| EU RoHS Indicator            | Yes   |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means   |
| Item Type                    | Flanged Single  |
| Material                     | Thermoplastic   |
| Material - Mounting Hardware | Screw Mounting  |
| Number Of Poles              | 1-Pole  |
| Series                       | Series 16   |
| Specifications               | <ul style="list-style-type: none"><li>• Base Compound - Thermoplastic Elastomer</li><li>• Contact Material - Brass</li><li>• Mounting Hole - 4x #10-32</li><li>• Retaining Screw Material - Nylon</li><li>• Termination - (2) 7/32 Socket Head Set Screws</li></ul> |

|       |                       |
|-------|-----------------------|
| Style | Double Set Screw Male |
| Type  | Receptacle            |
| UPC   | 783585112930          |

## Dimensions

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

## Electrical Ratings

|                            |                 |
|----------------------------|-----------------|
| Amperage Rating            | 400 A           |
| Connectivity               | Screw Terminals |
| Current / Amperage Rating  | 400 A           |
| Current Rating             | 400 A           |
| Phase                      | Single Phase    |
| Voltage Rating Description | 600V AC/DC      |
| Wattage                    | 240000          |

## Conductor Related

|           |                    |
|-----------|--------------------|
| Wire Size | #4 AWG to #4/0 AWG |
|-----------|--------------------|

## Certifications And Compliance

|                      |  |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• National Electric Code (NEC), ANSI/NFPA 70</li><li>• UL and cUL Listed</li><li>• UL Enclosure Types 3R, 4X, 12</li></ul> |
| Nema Rating          | Non-NEMA   |

## Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 25   |
| Pallet Quantity | 1575 |

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Single Pole Devices](#)  
[Specifications - HBLMRBK](#)  
[Warranty - Industrial & Commercial Products](#)

