

# Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Male-Male, Paralleling Tee, 300/400A 600V AC/DC, Single Conductor, Pre-Wired, White



By Hubbell Wiring Device-Kellems  
Catalog # [HBLPTW](#)

Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Male-Male, Paralleling Tee, 300/400A 600V AC/DC, Single Conductor, Pre-Wired, White

## Features

- Industrial Grade
- Female-Male-Male
- Paralleling Tee

## Application

High Ampacity

## Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of the device

## General

Catalog Number	HBLPTW
Color	White
EU RoHS Indicator	Contact Manufacturer
Insulation	Insulated Body
Item Type	T-Fittings
Material	Brass and Elastomer
Number Of Pins	1) In, 2) Out- Male-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Series 16
Specifications	<ul style="list-style-type: none"><li>• Body Material - Thermoplastic Elastomer</li></ul>

- Contact Material - Brass
- Product Type - T's" and Tri-Taps
- Tee and Tap Type - Paralleling "T" Fitting

Style

Paralleling Tee Femal-Male-Male

Type  
UPC

Tees and 3-Fers  
783585113166

## Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

## Certifications And Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

## Logistics

Carton Quantity	10
Pallet Quantity	1820

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Single Pole Devices](#)
- [Specifications - HBLPTW](#)
- [Warranty - Industrial & Commercial Products](#)