



Wiring Device-Kellems

## Heavy Duty Products, IEC Pin and Sleeve, Receptacle, Switched, 60/63A 380-415V AC, 3-Pole 4-Wire Grounding, NEMA4X/IP69K, With Pilot Contact

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5460R7W](#)

Heavy Duty Products, IEC Pin and Sleeve, Receptacle, Switched, 60/63A 380-415V AC, 3-Pole 4-Wire Grounding, NEMA4X/IP69K, With Pilot Contact

### Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

### General

Color	Red
Number Of Poles	3-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Receptacle
UPC	783585478647



### Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

### Conductor Related

Number Of Wires	4-Wire
-----------------	--------

### Logistics

Carton Quantity	6
-----------------	---

### Product Assets

[Catalog Page - Wiring G-6 Catalog page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL5460R7W-SPEC-EN | REV 1/2024