

Kellems Wire Management, Cord Connectors, Junior, .28"-.34", 3/8", Gray

By Hubbell Wiring Device-Kellems
Catalog # [HJ1006GPK25](#)

Kellems Wire Management, Cord Connectors, Junior, .28"-.34", 3/8", Gray

Application

Straight Male Connector

Performance

- Environmental - Flammability - Hubbell Juniors have a UL 94V-2 rating
- Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	HJ1006GPK25
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Junior Cord Connectors
Material	Nylon
Material - Mounting Hardware Series	Locknut or Tapped Opening Miniature
Specifications	<ul style="list-style-type: none">• Cord Diameter Range Inches (mm) - .28"-.34" (7.0-8.6)• Material - Nylon• NPT Hub Size - 3/8 Inch• Packaging - Bulk packed 25 per carton



Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	Connector
UPC	783585022987

Dimensions

Display Size	3/8" NPT
Hub Size	3/8"

Conductor Related

Conductor Range	0.28-0.34 in (7.0-8.6 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	IP66

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - HJ1006GPK25](#)
- [Warranty - Industrial & Commercial Products](#)