

Safety Products, PLUGOUT Lockout Device, Lockout Device, SIZE 1

By Hubbell Wiring Device-Kellems
Catalog # [HLD](#)

Twist-Lock® Devices, Accessories, PLUGOUT® Lockout device for attachable 20 and 30A plugs, straight body or angle types, with or without weatherproof covers, Yellow



Features

- PLUGOUT Lockout Device
- Lockout Device
- SIZE 1

Performance

- Environmental - Operating Temperature - Maximum continuous 140°F (60°C)
- minimum continuous -20°F (-29°C)
- Amperage - 15A
- Environmental - Optional storage position - Stores on cable when not in use
- Mechanical - Product Identification - Permanently molded into housing

General

Catalog Number	HLD
Color	Yellow
EU RoHS Indicator	Yes
Item Type	Accessories PLUGOUT® Lockout Devices
Legend	Instructions Molded Into Product
Lock Type	Accepts up to 4 Padlocks (not supplied)
Material	Polypropylene
Operating Temperature	Maximum continuous 60°C and minimum continuous -29 °C
Plug Type	All Standard Plugs and Connectors
Series	Accessory
Specifications	<ul style="list-style-type: none"> • Cord - 1.11" (28.2) max • Housing - UV stabilized polypropylene

- Number of Padlocks - 4 locks, 3/8" (9.5)
- Plug Length - 4 .75" (120.6) max

Style For 20 And 30A Hubbell Plugs And Others
UPC 783585001852

Dimensions

Dimensions	7.27 in x 4.27 in x 3.1 in
Display Size	Standard Size
Height	3.1 in
Length	7.27 in
Plug Dimensions	Min: 1.50" (38.1), Max: 2.75" (69.8) in
Weight	0.4 lb
Width	4.27 in

Conductor Related

Nema Color Yellow

Certifications And Compliance

Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 1
Pallet Quantity 660

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HLD](#)
[Warranty - Industrial & Commercial Products](#)