

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices,
Receptacles, Decorator Duplex,
Commercial Grade, Corrosion
Resistant, Smooth Face, 15A 125V,
2- Pole 3-Wire Grounding, 5-15R.**

By Hubbell Wiring Device-Kellems
Catalog # [IG15DR](#)

Straight Blade Devices, Receptacles, Decorator Duplex,
Commercial Grade, Corrosion Resistant, Smooth Face, 15A 125V,
2- Pole 3-Wire Grounding, 5-15R, Back and Side Wired, Orange.



General

Application	
Catalog Number	IG15DR
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current
	Electrical - Dielectric Voltage - Withstands 2,000V minimum
	Environmental - Flammability - UL 94 V-2
	Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
	Mechanical - Product Identification - Ratings are a permanent part of the device
	Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
	Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Commercial Specification Grade
Style	Style Line Decorator
Type	Standard Duplex
	Standard Duplex
UPC	783585146850

Dimensions

Dimensions	1.29 in x 0.83 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.29 in
Weight	0.15 lb
Width	0.83 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	Certified to CSA C22.2, No. 42 Fed. Spec. WC596 NEMA® WD-6 Compliant UL Listed to UL498 File No. E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-IG15DR-SPEC-EN | REV 6/2024