

Locking Devices, Twist-Lock®, Isolated Ground Industrial, Flush Receptacle, 30A 250V, 2-Pole 3- Wire Grounding, L6-30R, Screw Terminal, Orange

By Hubbell Wiring Device-Kellems
Catalog # IG2620



Twist-Lock® Devices, Single Flush Receptacle 30A, 250V AC, 2 Pole, 3 Wire Grounding, NEMA L6-30R, Isolated ground, nylon, Orange

Performance

- Electrical-Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Mechanical - Terminal Accommodation - #16 - #8 AWG solid or stranded copper wire
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
- Mechanical - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)

General

Catalog Number	IG2620
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	30A Single Flush Receptacle
Listings	<ul style="list-style-type: none">• UL 498• Fed.Spec. W-C-596• CSA C22.2 No.42
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Base - RTP• Contacts - Brass• Face - Nylon• Mounting Strap - Brass• Terminal Screws - #10 - 32 Brass
UPC	783585872346

Dimensions

Dimensions	3.28 in x 1.70 in x 1.31 in
Display Size	Standard Sized Product
Height	1.31 in
Length	3.28 in
Weight	0.2 lb
Width	1.7 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	6-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	2520

Product Assets

