

# Locking Devices, Twist-Lock®, Isolated Ground Industrial, Flush Receptacles, 30A 3-Phase Delta 250V AC, L15-30R, Screw Terminal

By Hubbell Wiring Device-Kellems  
Catalog # IG2720



Locking Devices, Twist-Lock®, Isolated Ground Industrial, Flush Receptacles, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-30R, Screw Terminal, Orange

## Application

Heavy Duty Industrial

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	IG2720
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	Single Flush Receptacles
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Base - RTP</li><li>• Contacts - Brass</li><li>• Face - Nylon</li><li>• Mounting Strap - Brass</li><li>• Terminal Screws - #10 - 32 Brass</li></ul>
UPC	783585872445

## Dimensions

Dimensions 3.28 in x 1.7 in x 1.23 in

Display Size	Standard Sized Product
Height	1.23 in
Length	3.28 in
Weight	0.35 lb
Width	1.7 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	250 VAC
Voltage Rating Description	250V

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Fed.Spec. W-C-596</li><li>• Listed to UL 498</li></ul>
Nema Rating	L15-30R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	2520

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - EdgeConnect™ Technology FAQ](#)  
[Specifications - IG2720](#)



**A Hubbell brand**