



# IG TVSS Duplex Receptacle with Light and Alarm, 15A 125V, 5-15R, Office White

By Hubbell Wiring Device-Kellems  
Catalog # IG5262OWSA



IG TVSS Duplex Receptacle with Light and Alarm, 15A 125V, 5-15R, Office White

## Application

Decorator Duplex with Light and Alarm

## General

Color	<ul style="list-style-type: none"> <li>Office White</li> <li>Blanc cassé</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> <li>Electrical - Protection Modes - Normal and Common Modes</li> <li>Electrical - Response Time - Approximately 5 ns</li> <li>Electrical - Transient Suppression - Peak Energy (10 X 100 <math>\mu</math>s), Peak Current (8 X 20 <math>\mu</math>s)</li> <li>Electrical - Voltage - 120V AC + 10% - 15%</li> <li>Environmental - Flammability - UL 94V-2</li> <li>Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)</li> </ul>
Response Time	5
Series	Specification Grade
Style	Isolated Ground
Type	<ul style="list-style-type: none"> <li>Duplex</li> <li>Duplex</li> </ul>
UPC	783585060651

## Dimensions

Display Size Standard

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>CSA Certified to Specification C22.2 No. 42</li> <li>Listed to UL Standards 498</li> <li>UL Listed File E2186</li> </ul>
Nema Rating	5-15R

## Logistics

Carton Quantity 10

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

