


**HUBBELL**  
Wiring Device-Kellems

**Straight Blade Devices,  
Receptacles, Duplex, Specification  
Grade, 2-Pole 3-Wire Grounding,  
20A 250V, 6-20R, Orange, Single  
Pack**

By Hubbell Wiring Device-Kellems  
Catalog # [IG5462](#)

Straight Blade Devices, Receptacles, Duplex, Specification  
Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, Orange,  
Single Pack



## General

Application	
Catalog Number	IG5462
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current
	Electrical - Dielectric Voltage - Withstands 2,000V minimum
	Environmental - Flammability - UL 94 V-2 or better
	Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
	Mechanical - Product Identification - Ratings are a permanent part of the device
	Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
	Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Standard Duplex
	Standard Duplex
UPC	783585880556

## Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Standard Sized Product
Height	1.05 in
Length	3.28 in
Weight	0.2 lb
Width	1.33 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	5000 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA 22.2, No. 42 File 285
	Guide RTRT Fed Spec WC596G
	NEMA® WD-6 Compliant
	UL Listed to UL498 File No. E2186
Nema Rating	6-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-IG5462-SPEC-EN | REV 6/2024