

Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Accessories, Back Box, For 30A 1" NPT Hub, Angled, Mounting Screws Included

By Hubbell Wiring Device-Kellems
Catalog # [MB302W](#)

Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Accessories, Back Box, For 30A 1" NPT Hub, Angled, Mounting Screws Included, Gray Cast Aluminum

Features

- Industrial Grade
- Accessories
- Back Box

Application

Metallic

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC
- Electrical - Max Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V-0 classification
- Environmental - Operating Temperatures - Max. Continuous: 75° C
- Min. Continuous: -40° C w/o impact
- Mechanical - Impact Resistance - In accordance with UL746C
- Mechanical - Product Identification - Identification and ratings are a part of the external label and molded into the receptacle mount
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions

General

Catalog Number	MB302W
Construction	Cast
EU RoHS Indicator	Yes
Item Type	Mounting Box
Knockouts	1" NPT Hub
Material	Aluminum



Material - Mounting Hardware
Number Of Outlets
Series
Specifications

Mounting Screws
Accepts 1-Device
Back Boxes and Adapters

- Assembly Screws - Stainless Steel
- Box Hub Size - 1" NPT
- Gaskets - Neoprene
- Hinge Spring - Stainless Steel

Style
Temperature Range
Type
UPC

30 Degree
Limited By Device
Back Box
783585010328

Dimensions

Display Size For 30 Amp Devices

Conductor Related

Cable Entry Through Hub

Certifications And Compliance

Industry Standard(s) UL Listed
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 2

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - MB302W](#)
[Warranty - Industrial & Commercial Products](#)