



# Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Accessories, Back Box, For 60A and 100A 1 1/2" NPT Hub, Angled

By Hubbell Wiring Device-Kellems  
 Catalog # [MB601003W](#)



Heavy Duty Insulgrip Pin and Sleeve Devices, Industrial Grade, Back Box, for 60A and 100A 1 1/2" NPT Hub, Angled, Mounting Screws Included

## Application

Metallic

## General

Construction	Cast
Item Type	Mounting Box
Knockouts	1 1/2" NPT Hub
Material	Aluminum
Material - Mounting Hardware	Mounting Screws
Number Of Outlets	Accepts 1-Device
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 3,000V AC</li> <li>• Electrical - Max Working Voltage - 600V AC RMS</li> <li>• Environmental - Flammability - UL94-5VA and V-O classification</li> <li>• Environmental - Operating Temperatures - Max. Continuous: 75° C</li> <li>• Min. Continuous: -40° C w/o impact</li> <li>• Mechanical - Impact Resistance - In accordance with UL746C</li> <li>• Mechanical - Product Identification - Identification and ratings are a part of the external label and molded into the receptacle mount</li> <li>• Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions</li> </ul>

Series

Back Boxes and Adapters

## Dimensions

Display Size For 60 and 100 Amp Devices

## Conductor Related

Cable Entry Through Hub

## Certifications and Compliance

Industry Standard(s) UL Listed  
 Standards - RoHS Compliance CM  
 Status

## Logistics

Carton Quantity 5

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

Style  
Temperature Range  
Type  
UPC

15 Degree  
Limited By Device  
Four-Way Back Box  
783585011240



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-MB601003W-SPEC-EN | REV 1/2024