

## Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Accessories, Back Box

By Hubbell Wiring Device-Kellems  
Catalog # [MB606W](#)



Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Accessories, Back Box, For 60A 1 1/2" NPT Hub, Feed Thru, Mounting Screws Included, Gray Cast Aluminum

### Features

- Industrial Grade
- Accessories
- Back Box

### Application

Metallic

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC
- Electrical - Max Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V-0 classification
- Environmental - Operating Temperatures - Max. Continuous: 75° C
- Min. Continuous: -40° C w/o impact
- Mechanical - Impact Resistance - In accordance with UL746C
- Mechanical - Product Identification - Identification and ratings are a part of the external label and molded into the receptacle mount
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions

### General

Catalog Number	MB606W
Construction	Cast
EU RoHS Indicator	Yes
Item Type	Mounting Box

### Knockouts

Material

Material - Mounting Hardware

Number Of Outlets

Series

Specifications

1 1/2" NPT Hub

Aluminum

Mounting Screws

Accepts 1-Device

Back Boxes and Adapters

- Assembly Screws - Stainless Steel
- Box Hub Size - 1 1/2" NPT
- Gaskets - Neoprene
- Hinge Spring - Stainless Steel

Style

Temperature Range

Type

UPC

Straight

Limited By Device

Feed-Thru Back Box

783585010823

### Dimensions

Display Size

For 60 Amp Devices

### Conductor Related

Cable Entry

Through Hub

### Certifications And Compliance

Industry Standard(s)

UL Listed

Standards - RoHS Compliance

CM

Status

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - MB606W](#)

[Warranty - Industrial & Commercial Products](#)