

Kellems Wire Management, Cord Connectors, 90 Degree Male .13-.19", 1/2", Nylon

By Hubbell Wiring Device-Kellems
Catalog # [NHC1020CR](#)



Kellems Wire Management, Cord Connectors, 90 Degree Male
.13-.19", 1/2", Nylon

Application

90 Degree Male- Form 2

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC.
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	NHC1020CR
Color	Gray
Color Code	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Gray Nylon
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Inches (mm) - .13"-.19" (3.2-4.7)• Form Size - F2• Material - Gray Nylon• NPT Hub Size - 1/2 Inch

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type
UPC

90° Male
783585208725

Dimensions

Display Size 1/2" NPT
Hub Size 1/2 "

Conductor Related

Conductor Range 0.13-0 .19 in (3.2- 4.7 mm)
Number of Conductors Single

Certifications And Compliance

Industry Standard(s) UL Listed
Nema Rating NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 25

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - NHC1020CR](#)
[Warranty - Industrial & Commercial Products](#)