

Kellems Wire Management, Cord Connectors, 90 Degree Male .25-.38", 1/2", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [NHC1022](#)



Kellems Wire Management, Cord Connectors, 90 Degree Male
.25-.38", 1/2", Aluminum

Application

90 Degree Male- Form 2

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC.
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	NHC1022
Color Code	White
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Inches (mm) - .25"-.38" (6.3-9.7)• Form Size - F2• Material - Aluminum• NPT Hub Size - 1/2 Inch

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type
UPC

90° Male
783585201221

Dimensions

Display Size 1/2" NPT
Hub Size 1/2 "

Conductor Related

Conductor Range 0.25- 0.38 in (6.3- 9.7 mm)
Number of Conductors Single

Certifications And Compliance

Industry Standard(s) UL Listed
Nema Rating NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 25
Pallet Quantity 7875

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - NHC1022](#)
[Warranty - Industrial & Commercial Products](#)