

## Kellems Wire Management, Cord Connectors, 90 Degree Male .50-.63", 3/4", Aluminum

By Hubbell Wiring Device-Kellems  
Catalog # [NHC1036](#)



Kellems Wire Management, Cord Connectors, 90 Degree Male  
.50-.63", 3/4", Aluminum

### Application

90 Degree Male- Form 3

### Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC.
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

### General

Catalog Number	NHC1036
Color Code	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none"><li>• Cord Diameter Inches (mm) - .50"- .63" (12.7-15.9)</li><li>• Form Size - F3</li><li>• Material - Aluminum</li><li>• NPT Hub Size - 3/4 Inch</li></ul>

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type  
UPC

90° Male  
783585201368

### Dimensions

Display Size  
Hub Size

3/4" NPT  
3/4"

### Conductor Related

Conductor Range  
Number of Conductors

0.5-0.63 in (12.7- 15.9 mm)  
Single

### Certifications And Compliance

Industry Standard(s)  
Nema Rating  
Standards - RoHS Compliance  
Status

UL Listed  
NEMA Type 4, 4X, 12 and 13  
CM

### Logistics

Carton Quantity  
Pallet Quantity

15  
4725

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - NHC1036](#)  
[Warranty - Industrial & Commercial Products](#)