

Kellems Wire Management, Cord Connectors, 90 Degree Male .50-.63", 3/4", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [NHC1036](#)



Kellems Wire Management, Cord Connectors, 90 Degree Male
.50-.63", 3/4", Aluminum

Application

90 Degree Male- Form 3

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC.
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	NHC1036
Color Code	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Inches (mm) - .50"- .63" (12.7-15.9)• Form Size - F3• Material - Aluminum• NPT Hub Size - 3/4 Inch

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type
UPC

90° Male
783585201368

Dimensions

Display Size
Hub Size

3/4" NPT
3/4"

Conductor Related

Conductor Range
Number of Conductors

0.5-0.63 in (12.7- 15.9 mm)
Single

Certifications And Compliance

Industry Standard(s)
Nema Rating
Standards - RoHS Compliance
Status

UL Listed
NEMA Type 4, 4X, 12 and 13
CM

Logistics

Carton Quantity
Pallet Quantity

15
4725

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - NHC1036](#)
[Warranty - Industrial & Commercial Products](#)