

Kellems Wire Management, Cord Connectors, 90 Degree Male .75-.88", 1", Aluminum

By Hubbell Wiring Device-Kellems

Catalog # [NHC1042](#)

Kellems Wire Management, Cord Connectors, 90 Degree Male
.75-.88", 1", Aluminum



General

Application	90 Degree Male- Form 4
Catalog Number	NHC1042
Color Code	Orchid
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Performance	Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC.
Series	Standard Duty
Temperature Rating	Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)
Type	90° Male
UPC	783585201429

Dimensions

Display Size	1" NPT
Hub Size	1"

Conductor Related

Conductor Range	0.75- 0.88 in (19.0- 22.2 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-NHC1042-SPEC-EN | REV 6/2024