

## Wallplates and Box Covers, Wallplate, Nylon, 2-Gang, 2) Toggle, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [NP2I](#)



Double Wallplate, Two Toggle

### General

Catalog Number	NP2I
Color	Ivory
Construction	Molded
Cutout	2) Toggle
EU RoHS Indicator	Yes
Item Type	Toggle Switch Plate
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	2-Gang
Operating Temperature	-40°C to 85 °C
Orientation	Vertical Mount
Size	Standard
Specifications	<ul style="list-style-type: none"><li>• Appearance - Smooth</li><li>• Mounting Screws - Steel painted, slotted head</li><li>• Plate Material - Nylon</li><li>• Plate Openings - Toggle switch</li><li>• Plate Type - 2-Gang</li></ul>
Style	2-Toggle
Type	Toggle
UPC	883778101687

### Dimensions

Dimensions	4.63 in x 4.68 in x 0.25 in
Display Size	Standard Sized
Height	0.25 in
Length	4.63 in
Thickness	0.25
Weight	0.05 lb
Width	4.68 in

### Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - NP2I](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)