



Wiring Device-Kellems

Kellems Wire Management, Liquidtight System, PolyTuff® Non-Metallic Liquidtight Fittings, 90 Degree Male Liquid-Tight Connector, 3/8", Gray

By Hubbell Wiring Device-Kellems
Catalog # [P0389NGY](#)



Kellems Wire Management, Liquidtight System, PolyTuff® Non-Metallic Liquidtight Fittings, 90 Degree Male Liquid-Tight Connector, 3/8", Gray

Features

- Nylon compression nut has a tapered dome to tighten ferrule onto conduit
- Neoprene O-ring provides liquidtight seal
- Non integral ferrule provides conduit seal and pullout protection

Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

General

Color	Gray
Material	Nylon
Performance	<ul style="list-style-type: none"> • Environmental - Flammability - UL 94X-2 • Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)
Style	90°
Type	PolyTuff® Non-Metallic Liquidtight Fittings
UPC	783585334158

Dimensions

Dimension - L Length Overall	2.91 in
mm	
Dimension - Thread Size	1/2" NPT
Height	1.98 in
Trade Size	3/8

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • UL Listed:UL50 Type 4X, 12 and 13
----------------------	--

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Safety Product Guide](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-P0389NGY-SPEC-EN | REV 1/2024