



Wiring Device-Kellems

Kellems Wire Management, Liquidtight System, PolyTuff® 90 Degree Male Liquid-Tight Connector, 3/4", Non-Metallic, Black



By Hubbell Wiring Device-Kellems
Catalog # [P0759NBK](#)

Kellems Wire Management, Liquidtight System, PolyTuff® 90 Degree Male Liquid-Tight Connector, 3/4", Non-Metallic, Black

Features

- Nylon compression nut has a tapered dome to tighten ferrule onto conduit
- Neoprene O-ring provides liquidtight seal
- Non integral ferrule provides conduit seal and pullout protection

Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

General

Color	Black
Material	Nylon
Performance	<ul style="list-style-type: none"> • Environmental - Flammability - UL 94X-2 • Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)
Style	90°
Type	PolyTuff® Non-Metallic Liquidtight Fittings
UPC	783585498805

Dimensions

Dimension - L Length Overall	3.17 in
mm	
Dimension - Thread Size	3/4" NPT
Height	2.29 in
Trade Size	3/4

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • UL Listed:UL50 Type 4X, 12 and 13
----------------------	--

Logistics

Carton Quantity	20
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.