

## Kellems Wire Management, Liquidtight System, PolyTuff® 90 Degree Male Liquid-Tight Connector, 3/4", Non-Metallic, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [P0759NGY](#)



Kellems Wire Management, Liquidtight System, PolyTuff® 90  
Degree Male Liquid-Tight Connector, 3/4", Non-Metallic, Gray

### Application

- Fittings are to be used with PolyTuff® I and PolyTuff® II

### Performance

- Environmental - Flammability - UL 94X-2
- Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)

### General

Catalog Number	P0759NGY
Color	Black
EU RoHS Indicator	Yes
Material	Nylon
Specifications	<ul style="list-style-type: none"><li>Fitting - Nylon</li><li>Lockwasher - Zinc plated steel</li><li>Sealing Ring - Elastomer</li></ul>
Style	90°
Type	PolyTuff® Non-Metallic Liquidtight Fittings
UPC	783585810027

### Dimensions

Dimension - L Length Overall mm	3.17 in
Dimension - Thread Size	3/4" NPT
Height	2.29 in
Trade Size	3/4

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>CSA Certified</li><li>UL Listed:UL50 Type 4X, 12 and 13</li></ul>
----------------------	---

Standards - RoHS Compliance Status	CM
---------------------------------------	----

### Logistics

Carton Quantity	20
Pallet Quantity	4320

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - P0759NGY](#)  
[Warranty - Industrial & Commercial Products](#)