



Wiring Device-Kellems

# Kellems Wire Management, Liquidtight System, PolyTuff® Straight Male, Liquid Tight Connector, 3/4", Non-Metallic, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [P075NGYA](#)



Kellems Wire Management, Liquidtight System, PolyTuff®  
Straight Male, Liquid Tight Connector, 3/4", Non-Metallic, Gray

## Features

- Nylon compression nut has a tapered dome to tighten ferrule onto conduit
- Neoprene O-ring provides liquidtight seal
- Non integral ferrule provides conduit seal and pullout protection

## Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

## General

Color	<ul style="list-style-type: none"> <li>• Gray</li> <li>• Gris</li> </ul>
Material	Nylon
Performance	<ul style="list-style-type: none"> <li>• Environmental - Flammability - UL 94X-2</li> <li>• Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)</li> </ul>
Style	Straight
Type	<ul style="list-style-type: none"> <li>• PolyTuff® Non-Metallic Liquidtight Fittings</li> <li>• PolyTuff® Non-Metallic Liquidtight Fittings</li> </ul>
UPC	783585339177

## Dimensions

Trade Size 3/4

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified</li> <li>• UL Listed:UL50 Type 4X, 12 and 13</li> </ul>
----------------------	--

Standards - RoHS Compliance CM Status

## Logistics

Carton Quantity 25

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-P075NGYA-SPEC-EN | REV 1/2024