



# Kellems Wire Management, Liquidtight System, PolyTuff® 90 Degree Male Liquid-Tight Connector, 1", Non-Metallic, Black

By Hubbell Wiring Device-Kellems  
Catalog # [P1009NBK](#)



Kellems Wire Management, Liquidtight System, PolyTuff® 90  
Degree Male Liquid-Tight Connector, 1", Non-Metallic, Black

## Features

- Nylon compression nut has a tapered dome to tighten ferrule onto conduit
- Neoprene O-ring provides liquidtight seal
- Non integral ferrule provides conduit seal and pullout protection

## Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

## General

Color	Black
Material	Nylon
Performance	<ul style="list-style-type: none"><li>• Environmental - Flammability - UL 94X-2</li><li>• Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)</li></ul>
Style	90°
Type	PolyTuff® Non-Metallic Liquidtight Fittings
UPC	783585810034

## Dimensions

Dimension - L Length Overall mm	3.96 in
Dimension - Thread Size	1" NPT
Height	2.83 in
Trade Size	1

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified</li><li>• UL Listed:UL50 Type 4X, 12 and 13</li></ul>
----------------------	---

Standards - RoHS Compliance Status	CM
---------------------------------------	----

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-P1009NBK-SPEC-EN | REV 1/2024