



Kellems Wire Management, Liquidtight System, PolyTuff® 90 Degree Male Liquid Tight Connector, 1 1/4", Non-Metallic, Black

By Hubbell Wiring Device-Kellems
Catalog # [P1259NBK](#)



Kellems Wire Management, Liquidtight System, PolyTuff® 90
Degree Male Liquid Tight Connector, 1 1/4", Non-Metallic, Black

Features

- Nylon compression nut has a tapered dome to tighten ferrule onto conduit
- Neoprene O-ring provides liquidtight seal
- Non integral ferrule provides conduit seal and pullout protection

Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

General

Color	Black
Material	Nylon
Performance	<ul style="list-style-type: none">• Environmental - Flammability - UL 94X-2• Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)
Style	90°
Type	PolyTuff® Non-Metallic Liquidtight Fittings
UPC	783585334387

Dimensions

Trade Size	1 1/4
------------	-------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Listed:UL50 Type 4X, 12 and 13
----------------------	---

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Wire Management Solutions Brochure](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.