



Wiring Device-Kellems

# Kellems Wire Management, Liquidtight System, PolyTuff® 90 Degree Male Liquid Tight Connector, 1 1/4", Non-Metallic, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [P1259NGY](#)



Kellems Wire Management, Liquidtight System, PolyTuff® 90 Degree Male Liquid Tight Connector, 1 1/4", Non-Metallic, Gray

## Features

- Nylon compression nut has a tapered dome to tighten ferrule onto conduit
- Neoprene O-ring provides liquidtight seal
- Non integral ferrule provides conduit seal and pullout protection

## Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

## General

Color	Gray
Material	Nylon
Performance	<ul style="list-style-type: none"> <li>• Environmental - Flammability - UL 94X-2</li> <li>• Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)</li> </ul>
Style	90°
Type	PolyTuff® Non-Metallic Liquidtight Fittings
UPC	783585334356

## Dimensions

Trade Size 1 1/4

## Certifications and Compliance

- |                      |  |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none"> <li>• CSA Certified</li> <li>• UL Listed:UL50 Type 4X, 12 and 13</li> </ul> |
|----------------------|--|

## Logistics

Carton Quantity 5

## Product Assets

- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.