

Non-Metallic Raceway, BaseTrak, 2 or 3 Channel, Internal Elbow, Base and Cover

By Hubbell Wiring Device-Kellems
Catalog # [PB3IEBCA](#)



Non-Metallic Raceway, BaseTrak, 2 or 3 Channel, Internal Elbow, Base and Cover

Features

- Full capacity 1¼ in. bend radius internal elbow

Application

Internal Elbow Base and Cover

Performance

- Environmental - Flame Rating - UL94V-0
- Environmental - Temperature Range - -25.6° to 158° F

General

Catalog Number	PB3IEBCA
Color	Office White
Cover Type	Removable
EU RoHS Indicator	Contact Manufacturer
Item Type	PB2 and PB3 BaseTrak Series
Material	Non-Metallic
Series	<ul style="list-style-type: none">• PB2• PB3
Specifications	<ul style="list-style-type: none">• Crush Resistance - 300 lbs.

Style

Sub Brand

Type

UPC

- Impact Resistance - 5 ft. lbs.

- Material - UV Stabilized PVC

Internal

Non-Metallic Raceway

Elbows

783585310107

Certifications And Compliance

Industry Standard(s)

UL 5A

Standards - RoHS Compliance

CM

Status

Logistics

Carton Quantity

10

Pallet Quantity

320

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - PB3IEBCA](#)

[Warranty - Industrial & Commercial Products](#)

