



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessories, Male Closure Cap, For 60A All Wire, Gray Non-Metallic

By Hubbell Wiring Device-Kellems
Catalog # [PC60](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessories, Male Closure Cap, For 60A All Wire, Gray Non-Metallic

Application

All 60 and 63 Amp

General

Color	<ul style="list-style-type: none"> • Gray • Gris
Environmental Conditions	Watertight
Item Type	Plug Cover
Material	Composite
Material - Mounting Hardware	Cord Mounted
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 3,000V AC • Electrical - Max Working Voltage - 600V AC RMS • Environmental - Flammability - UL94-5VA and V-0 classification • Environmental - Moisture Resistance - IP67 Suitability • Environmental - Operating Temperatures - Max. Continuous:75°C • Min. Continuous:-40°C w/o impact • Mechanical - Impact Resistance - In accordance with UL746C • Mechanical - Product Identification - Ratings are a part of the external label and molded into the receptacle mount • Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions

Dimensions

Display Size Standard Sized

Electrical Ratings

Connectivity Pressure Terminal Screws

Conductor Related

Cord Type All Portable

Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Hubbell PRO Pin & Sleeve Brochure](#)
[Warranty - Industrial & Commercial Products](#)

Series	Accessories
Style	Fits all 60 and 63A
Type	<ul style="list-style-type: none">• Closure Caps• Closure Caps
UPC	783585373607



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-PC60-SPEC-EN | REV 1/2024