



Kellems Wire Management, Liquidtight System, SwivelLok® Multi-Position Male Liquid Tight Connector, 3/8", Non-Metallic, Black

By Hubbell Wiring Device-Kellems
Catalog # [PSO389NBK](#)



Kellems Wire Management, Liquidtight System, SwivelLok®
Multi-Position Male Liquid Tight Connector, 3/8", Non-Metallic,
Black

Features

- Nylon compression nut has a tapered dome to tighten ferrule onto conduit
- Neoprene O-ring provides liquidtight seal
- Non integral ferrule provides conduit seal and pullout protection
- Swiveled to any position from straight to 90°

Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

General

Color	<ul style="list-style-type: none"> • Black • Noir
Material	Nylon
Performance	<ul style="list-style-type: none"> • Environmental - Flammability - UL 94X-2 • Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)
Style Type	SwivelLok® Multi-Position <ul style="list-style-type: none"> • PolyTuff® SwivelLok® Non-Metallic Liquidtight Fittings • PolyTuff® SwivelLok® Non-Metallic Liquidtight Fittings
UPC	783585525426

Dimensions

Trade Size 3/8

Certifications and Compliance

Industry Standard(s)

- CSA Certified
- UL Listed:UL50 Type 4X, 12 and 13

Standards - RoHS Compliance CM Status

Logistics

Carton Quantity 25

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Wire Management Solutions Brochure](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-PSO389NBK-SPEC-EN | REV 1/2024