

## Kellems Wire Management, Liquidtight System, SwivelLok® Flexible Conduit Kit, 1/2" X6, 2 PS0509NGY, 6' G1050

By Hubbell Wiring Device-Kellems  
Catalog # [PS05GYKIT](#)



Kellems Wire Management, Liquidtight System, SwivelLok®  
Flexible Conduit Kit, 1/2" X6, 2 PS0509NGY, 6' G1050

### Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

### Performance

- Environmental - Flammability - UL 94X-2
- Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)

### General

Catalog Number	PS05GYKIT
Color	Gray
EU RoHS Indicator	No
Environmental Conditions	Suitable For Use In Wet Locations When A Listed Sealing Ring Is Used Between Box And Fitting
Item Type	PolyTuff Kit
Load Capacity	Extra Flexible
Material	Nylon
Material - Mounting Hardware	Between Enclosure and Conduit
Specifications	<ul style="list-style-type: none"><li>• Material - Nylon</li><li>• Sealing Ring - Neoprene</li></ul>
Style	SwivelLok® Kit
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)

Type	SwivelLok® Flexible Conduit Kit
UPC	783585339658

### Dimensions

Display Size	1/2"
Trade Size	1/2

### Electrical Ratings

Connectivity	Cap Nut
--------------	---------

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified</li><li>• UL Listed:UL50 Type 4X, 12 and 13</li></ul>
----------------------	---

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - PS05GYKIT](#)
- [Warranty - Industrial & Commercial Products](#)