

Kellems Wire Management, Liquidtight System, SwivelLok® Flexible Conduit Kit, 3/4" X6, 2 PS0759NGY, 6' G1075

By Hubbell Wiring Device-Kellems
Catalog # [PS07GYKIT](#)



Kellems Wire Management, Liquidtight System, SwivelLok®
Flexible Conduit Kit, 3/4" X6, 2 PS0759NGY, 6' G1075

Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

Performance

- Environmental - Flammability - UL 94X-2
- Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	PS07GYKIT
Color	Gray
EU RoHS Indicator	No
Environmental Conditions	Suitable For Use In Wet Locations When A Listed Sealing Ring Is Used Between Box And Fitting
Item Type	PolyTuff Kit
Load Capacity	Extra Flexible
Material	Nylon
Material - Mounting Hardware	Between Enclosure and Conduit
Specifications	<ul style="list-style-type: none">• Material - Nylon• Sealing Ring - Neoprene
Style	SwivelLok® Kit
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)

Type	SwivelLok® Flexible Conduit Kit
UPC	783585396668

Dimensions

Display Size	3/4"
Trade Size	3/4

Electrical Ratings

Connectivity	Cap Nut
--------------	---------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Listed:UL50 Type 4X, 12 and 13
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - PS07GYKIT](#)
- [Warranty - Industrial & Commercial Products](#)