

Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 6', 20A 125V, 1-Circuit, 6) Duplex



By Hubbell Wiring Device-Kellems
Catalog # [PT206112](#)

Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 6', 20A 125V, 1-Circuit, 6) Duplex

Performance

- Electrical - Crush Resistance - 300 lbs.
- Electrical - Impact Resistance - 5 ft. lbs
- Electrical - Receptacle Rating - NEMA 5-15R & 5-20R
- Environmental - Flame Rating - UL94V-0
- Environmental - Temperature Range - -25.6° to 158° F
- Mechanical - Wire - #12 AWG Stranded Copper

General

Catalog Number	PT206112
Color	Office White
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	6
Series	Non-Metallic
Specifications	<ul style="list-style-type: none">• Material - UV Stabilized PVC• Number of Receptacles - 6 Duplex• PlugTrak Amperage - 20A• PlugTrak Length - 6 Foot• Receptacle Face - Thermoplastic• Spacing - 12 Inch
Style	Standard
Type	Single Circuit

UPC 783585091051

Dimensions

Length 6 ft

Electrical Ratings

Current / Amperage Rating 20 A
Voltage Rating 125 VAC

Conductor Related

Wire Size #12 AWG THHN

Certifications And Compliance

Industry Standard(s)

- CSA Standard C22.2 no. 62
- E118895 / E119190
- UL Standard UL 5A

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - PT206112](#)
[Warranty - Industrial & Commercial Products](#)