

## Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Three Way Toggle, 15A 120V AC, Self Grounding, Side Wired

By Hubbell Wiring Device-Kellems  
Catalog # [RC103W](#)



One Single-Pole One 3-Way Toggle Combination Device,  
Residential 15A 120V AC, Self Grounding, Side Wired

### Application

- Residential

### Performance

Environmental - Operating temperature - -20°C to 60°C

### General

Action	Snap Switch
Actuator	Toggle
Catalog Number	RC103W
Contact Configuration	Two Position
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Switch Combo Devices
Material - Mounting Hardware	Mounting Screws
Number Of Poles	1) Single Pole, 1) Three Way
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
UPC	883778109911

### Dimensions

Display Size

Standard Size

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC
Wattage	1800

### Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

### Logistics

Carton Quantity	10
Pallet Quantity	7200

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Residential Catalog](#)  
[Specifications - RC103W](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)