

Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [RD600RI](#)

Switches and Lighting Controls, Dimmer, Rotary, Single Pole,
600W 120V AC, Ivory

General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Catalog Number	RD600RI
Color	Ivory
Construction	Metal Strap, Polycarbonate Front
EU RoHS Indicator	No
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Specifications	<ul style="list-style-type: none">Product Type - Rotary DimmersTermination - Single Pole
Style	Rotary Dimmer
Type	Incandescent
UPC	883778117053

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	5 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	600 W

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - RD600RI](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

