

# Switches and Lighting Controls, Dimmer, Rotary, Single Pole and Three Way, CFL and LED Loads, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [RDVCL153PI](#)



Switches and Lighting Controls, Dimmer, Rotary, Single Pole and  
Three Way, CFL and LED Loads, Ivory

## General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Catalog Number	RDVCL153PI
Color	Ivory
Construction	Metal Strap, Polycarbonate Front
EU RoHS Indicator	No
Environmental Conditions	Indoor Use Only
Material - Mounting Hardware	Screws and Wire connectors included
Number Of Poles	Single Pole / 3-Way
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Specifications	<ul style="list-style-type: none"><li>Product Type - Decorator Dimmer</li><li>Termination - Single Pole/Three Way</li></ul>
Style	Rocker Dimmer
Type	LED/CFL
UPC	883778304521

## Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

## Electrical Ratings

Amperage Rating	1.25 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	150 W

## Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	6
-----------------	---

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - RDVCL153PI](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)