

Switches and Lighting Controls, Dimmer, Rotary, Single Pole and Three Way, CFL and LED Loads, White

By Hubbell Wiring Device-Kellems
Catalog # [RDVCL153PW](#)



Switches and Lighting Controls, Dimmer, Rotary, Single Pole and
Three Way, CFL and LED Loads, White

General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Catalog Number	RDVCL153PW
Color	White
Construction	Metal Strap, Polycarbonate Front
EU RoHS Indicator	No
Environmental Conditions	Indoor Use Only
Material - Mounting Hardware	Screws and Wire connectors included
Number Of Poles	Single Pole / 3-Way
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Specifications	<ul style="list-style-type: none">Product Type - Decorator DimmerTermination - Single Pole/Three Way
Style	Rocker Dimmer
Type	LED/CFL
UPC	883778304545

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	1.25 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	150 W

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	24
Pallet Quantity	2592

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - RDVCL153PW](#)
[Warranty - tradeSELECT™ and netSELECT®](#)