

Lamp Holders and Sockets, Medium Base, Cleat Socket, 660W 250V, Porcelain

By Hubbell Wiring Device-Kellems
Catalog # [RL152](#)

Lamp Holders and Sockets, Medium Base, Cleat Socket, 660W 250V, Porcelain

Features

- Medium Base
- Cleat Socket
- 660W 250V
- Porcelain

Application

Medium Base Surface and Sign Mount

General

Catalog Number	RL152
Color	White
EU RoHS Indicator	Yes
Item Type	Replacement Incandescent Lampholders
Lamp Size	Medium Base
Material	Composite
Material - Mounting Hardware	1 Piece Surface Mount
Series	Lampholders
Specifications	<ul style="list-style-type: none">• Lamp Type - E26 socket• Material - Porcelain• Mounting - 1 piece, surface mount



Type	Surface & Sign Mount, Medium Base
UPC	883778112201

Electrical Ratings

Amperage Rating	2.64 A
Connectivity	Screw Terminals
Current / Amperage Rating	2.64 A
Current Rating	2.64 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

Certifications And Compliance

Industry Standard(s)	C/US UL Listed
----------------------	----------------

Logistics

Carton Quantity	50
Pallet Quantity	4900

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - RL152](#)
[Warranty - tradeSELECT™ and netSELECT®](#)