

## TradeSelect, Straight Blade, Female Connector, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15R, .40" Cord Diameter, White

By Hubbell Wiring Device-Kellems  
Catalog # [RP649](#)



TradeSelect, Straight Blade, Female Connector, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15R, .40" Cord Diameter, White

### Features

- Female Connector
- 15A 125V
- 2-Pole 2-Wire Non-Grounding

### Application

Trade Select Residential Devices

### General

Catalog Number	RP649
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Plugs & Connectors
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plugs
UPC	883778112577

### Dimensions

Display Size	Standard
--------------	----------

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC

### Conductor Related

Conductor Range	#16 AWG to #14 AWG
Number of Conductors	2-Wire Non-Grounding

### Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	1-15R

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - RP649](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)