

TradeSelect, Straight Blade, Female Connector, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15R, .40" Cord Diameter, White

By Hubbell Wiring Device-Kellems
Catalog # [RP649](#)



TradeSelect, Straight Blade, Female Connector, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15R, .40" Cord Diameter, White

Features

- Female Connector
- 15A 125V
- 2-Pole 2-Wire Non-Grounding

Application

Trade Select Residential Devices

General

Catalog Number	RP649
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Plugs & Connectors
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plugs
UPC	883778112577

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Number of Conductors	2-Wire Non-Grounding

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	1-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - RP649](#)
[Warranty - tradeSELECT™ and netSELECT®](#)