

## TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 3-Wire Non- Grounding, 10-50R, Flush Mount, Black

By Hubbell Wiring Device-Kellems  
Catalog # [RR350F](#)



tradeSELECT® Straight Blade Residential Grade, Single, 50A  
125/250V, 3-Pole 3-Wire Non-Grounding, 10-50R, Flush Mount

### Features

- Residential Grade
- Receptacles
- Single

### Application

Residential Range and Dryer Devices

### General

|                              |                                                 |
|------------------------------|-------------------------------------------------|
| Catalog Number               | RR350F                                          |
| Color                        | Black                                           |
| EU RoHS Indicator            | Yes                                             |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means |
| Material                     | Thermoplastic                                   |
| Material - Mounting Hardware | Screw Mounting                                  |
| Number Of Poles              | 3-Pole                                          |
| UPC                          | 883778100802                                    |

### Dimensions

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

### Electrical Ratings

|                           |                          |
|---------------------------|--------------------------|
| Amperage Rating           | 30 A                     |
| Connectivity              | Pressure Terminal Screws |
| Current / Amperage Rating | 30 A                     |
| Current Rating            | 30 A                     |
| Phase                     | Single Phase             |
| Voltage Rating            | 125/250 VAC              |
| Wattage                   | 7500                     |

### Conductor Related

|                 |                      |
|-----------------|----------------------|
| Number Of Wires | 3-Wire Non-Grounding |
| Wire Size       | #6 AWG               |

### Certifications And Compliance

|                      |           |
|----------------------|-----------|
| Industry Standard(s) | UL Listed |
| Nema Rating          | 10-30R    |

### Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 10   |
| Pallet Quantity | 2800 |

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - RR350F](#)

[Warranty - tradeSELECT™ and netSELECT®](#)