

TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Surface Mount, Black

By Hubbell Wiring Device-Kellems
Catalog # [RR450](#)



tradeSELECT® Straight Blade Residential Grade, Single, 50A
125/250V, 3-Pole 4-Wire Grounding, 14-50R, Surface Mount

Features

- Flush Mount for 1- or 2-Gang Box
- Residential Range and Dryer Receptacle

Application

Residential Range and Dryer Devices

General

Catalog Number	RR450
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Heavy Duty
Type	Single Receptacle
UPC	883778100833

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	50 A
-----------------	------

Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	12500

Conductor Related

Number Of Wires	4-Wire
Wire Size	#6 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	14-50R

Logistics

Carton Quantity	10
Pallet Quantity	1960

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Residential Catalog](#)
- [Specifications - RR450](#)
- [Warranty - tradeSELECT™ and netSELECT®](#)