

# TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 4- Wire Grounding, 14-50R, Flush Mount, White

By Hubbell Wiring Device-Kellems  
Catalog # [RR450FW](#)



tradeSELECT® Straight Blade Residential Grade, Single, 50A  
125/250V, 3-Pole 4-Wire Grounding, 14-50R, Flush Mount

## Features

- Sequenced contacts assure protection
- Catalog number, ratings and certifications molded in face
- One piece design power and ground contacts

## Application

Residential Range and Dryer Devices

## General

Catalog Number	RR450FW
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Heavy Duty
Style	Smooth Face
Type	Single Receptacle
UPC	883778100765

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	12500

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#6 AWG

## Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	14-50R

## Logistics

Carton Quantity	10
Pallet Quantity	2800

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Residential Catalog](#)  
[Specifications - RR450FW](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)