

TradeSelect, Cube Tap, Duplex to 6 Outlet, 15A 125V AC, 2-Pole 3-Wire Grounding, 5-15R, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [RT600I](#)



TradeSelect, Cube Tap, Duplex to 6 Outlet, 15A 125V AC, 2-Pole 3-Wire Grounding, 5-15R, Ivory

Features

- Cube Tap
- Duplex to 6 Outlet
- 15A 125V AC
- 2-Pole 3-Wire Grounding

Application

Six Outlet Plug-In

General

Catalog Number	RT600I
Color	Ivory
EU RoHS Indicator	Yes
Insulation	Insulated Body
Item Type	Taps
Material	Composite
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Taps & Adaptors

UPC 883778112409

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC
Wattage	1875

Certifications And Compliance

Industry Standard(s) C/US UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - RT600I](#)
[Warranty - tradeSELECT™ and netSELECT®](#)