

Spider Portable Power, Complete Unit, Straight Blade Style, 7) 20A 125V Straight Blade Receptacles, 1) 50A, 125/250V Inlet and 1) 50A 125/250V Outlet



By Hubbell Wiring Device-Kellems
Catalog # SBSB1A

Temporary Power Products, Spider Portable Power, Complete Unit, Straight Blade Style, With 7) 20A 125V Straight Blade Receptacles, 1) 50A, 125/250V Locking Inlet and 1) 50A 125/250V Locking Outlet

Application

Heavy Duty Portable

Performance

Environment - Moisture Resistance - Indoor and outdoor wet and dry locations

General

| | |
|------------------------------|---|
| Catalog Number | SBSB1A |
| Color | Yellow |
| EU RoHS Indicator | No |
| Environmental Conditions | Indoor and Outdoor |
| Item Type | Straight Blade Singles |
| Material | Thermoplastic |
| Material - Mounting Hardware | Non-Mounted, Portable |
| Number Of Poles | 3-Pole |
| Series | Spider II |
| Specifications | <ul style="list-style-type: none">Code Compliance - NEC®, ANSI/NFPA 70Enclosure Type - 3R, rainproof, suitable for use in damp locations |
| Type | 7-20A, 125V Straight Blade Receptacles, 1-50A, 125/250V Locking Inlet, 1-50A 125/250V Locking Outlet |
| UPC | 783585370873 |

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

| | |
|----------------------------|--------------|
| Amperage Rating | 50 A |
| Connectivity | Pre-Wired |
| Current / Amperage Rating | 50 A |
| Current Rating | 50 A |
| Phase | Single Phase |
| Voltage Rating | 120/240 VAC |
| Voltage Rating Description | 120/240 VAC |
| Wattage | 12500 |

Conductor Related

| | |
|-----------------|------------------------|
| Number Of Wires | 4-Wire Grounding |
| Wire Size | #10 AWG Min #6 AWG Max |

Certifications And Compliance

| | |
|----------------------|----------------------------------|
| Industry Standard(s) | UL 1640 cUL and CSA, UL 943 |
| Nema Rating | 7) 5-20R, 1) 50A Non-NEMA In/Out |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 1 |
| Pallet Quantity | 9 |

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - SBSB1A](#)
[Warranty - Industrial & Commercial Products](#)