

# Spider Portable Power, Complete Unit, Straight Blade Style, With 6) 20A 125V Receptacles- 1) 30A 250V Locking Receptacle- 1) 50A 125/250V Inlet and



By Hubbell Wiring Device-Kellems  
Catalog # [SBSB2](#)

Temporary Power Products, Spider Portable Power, Complete Unit, Straight Blade Style, With 6) 20A 125V Receptacles- 1) 30A 250V Locking Receptacle- 1) 50A 125/250V Inlet and

## Application

Heavy Duty Portable

## Performance

Environment - Moisture Resistance - Indoor and outdoor wet and dry locations

## General

Catalog Number	SBSB2
Color	Yellow
EU RoHS Indicator	No
Environmental Conditions	Indoor and Outdoor
Item Type	Straight Blade Singles
Material	Thermoplastic
Material - Mounting Hardware	Non-Mounted, Portable
Number Of Poles	3-Pole
Series	Spider II
Specifications	<ul style="list-style-type: none"><li>Code Compliance - NEC®, ANSI/NFPA 70</li><li>Enclosure Type - 3R, rainproof, suitable for use in damp locations</li></ul>
Type	6-20A, 125V Straight Blade Receptacles, 1-30A, 250V Locking Receptacle, 1-50A 125/250V Inlet, 1-50A 125/250V Locking Outlet
UPC	783585369471

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Pre-Wired
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	120/240 VAC
Voltage Rating Description	120/240 VAC
Wattage	12500

## Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	#10 AWG Min #6 AWG Max

## Certifications And Compliance

Industry Standard(s)	UL 1640 cUL and CSA, UL 943
Nema Rating	6) 5-20R, 1) L6-30R, 1) 50A Non-NEMA In/Out

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - SBSB2](#)  
[Warranty - Industrial & Commercial Products](#)