



# Industrial Grade, Lever Actuated, Switched Twist-Lock Enclosure With pre-wired HBL2730 Receptacle, 30A Twist-Lock®, 3 Phase 480 V AC, NEMA L16-30R.

By Hubbell Wiring Device-Kellems  
Catalog # [SE2730A](#)



Switches and Lighting Controls, Industrial Grade, Lever Actuated, Switched Twist-Lock Enclosure With pre-wired HBL2730 Receptacle, 30A Twist-Lock®, 3 Phase 480 V AC, NEMA L16-30R, Terminal Screws, Gray.

## Features

- Lockable handle provides lockout protection for greater safety and complies with OSHA lockout requirements
- Horsepower rated switch
- Large receptacle gasketless door and hinge assembly
- Heavy-duty internal frame bonds conduit and all grounds and has a DIN rail to accommodate the switch

## General

Color	Gray
Horsepower - Maximum	10
Item Type	Switched Safety Enclosures
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage</li> <li>• Electrical - Dielectric Voltage - Withstands 3,000V minimum</li> <li>• Electrical - Max. Working Voltage - 600V RMS</li> <li>• Electrical - Operations - Mechanical 10,000 cycles</li> <li>• Electrical 6,000 cycles</li> <li>• Environmental - Flammability - UL94 - 5 VA and VO classification</li> <li>• Environmental - Moisture Resistance - IP54 suitability</li> <li>• Environmental - Operating Temperature - Maximum continuous +75°C Minimum continuous -40°C</li> <li>• Environmental - UV Resistance - All materials are UV stabilized</li> <li>• Mechanical - Impact</li> </ul>

## Dimensions

Dimensions	11.38 in x 4.88 in x 4.38 in
Height	4.38 in
Length	11.38 in
Weight	4 lb
Width	4.88 in

## Electrical Ratings

Dielectric Strength	Withstands 3,000V minimum
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified Type 3R and 12K Enclosure Rating</li> <li>• Listed to UL Standard</li> </ul>
Nema Rating	L16-30R

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Catalog Page - Wiring B-39 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

Resistance - In accordance with UL 746C

- Mechanical - Mounting - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label and receptacle face
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Type  
UPC

Switched Enclosure  
783585006352



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-SE2730A-SPEC-EN | REV 1/2024