

Kellems Wire Management, Cord Connectors, European Style, .17-.45", 1/2", Black

By Hubbell Wiring Device-Kellems
Catalog # [SEC50BA](#)



Kellems Wire Management, Cord Connectors, European Style, .17-.45", 1/2", Black

Application

- Straight Male Connector

Performance

- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperatures - -22°F to 225°F (-30°C to 107°C)
- Environmental - Protection Class - IP66 Suitability

General

Catalog Number	SEC50BA
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Low Profile Cord Connectors
Material	Non-Metallic
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Low Profile NPT
Specifications	<ul style="list-style-type: none">• Body - Nylon• Cord Diameter Inches (mm) - .17"-.45" (4.3-11.4)• Gland - Buna N• NPT HUB Size - 1/2 Inch
Temperature Rating	Minimum -22 Deg F to 225 Deg F (-30 Deg C to 107 Deg C)

Type	Connector
UPC	783585018126

Dimensions

Display Size	1/2" NPT
Hub Size	1/2 "

Conductor Related

Conductor Range	0.17-0.45 in (4.3-11.4 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	IP66
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	50
Pallet Quantity	10800

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - SEC50BA](#)
- [Warranty - Industrial & Commercial Products](#)