

## Kellems Wire Management, Cord Connectors, European Style, .17-.45", 1/2", Gray

By Hubbell Wiring Device-Kellems  
Catalog # [SEC50GA](#)



Kellems Wire Management, Cord Connectors, European Style, .17-.45", 1/2", Gray

### Application

Straight Male Connector

### Performance

- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperatures - -22°F to 225°F (-30°C to 107°C)
- Environmental - Protection Class - IP66 Suitability

### General

Catalog Number	SEC50GA
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Low Profile Cord Connectors
Material	Non-Metallic
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Low Profile NPT
Specifications	<ul style="list-style-type: none"><li>• Body - Nylon</li><li>• Cord Diameter Inches (mm) - .17"-.45" (4.3-11.4)</li><li>• Gland - Buna N</li><li>• NPT HUB Size - 1/2 Inch</li></ul>
Temperature Rating	Minimum -22 Deg F to 225 Deg F (-30 Deg C to 107 Deg C)

Type	Connector
UPC	783585018102

### Dimensions

Display Size	1/2" NPT
Hub Size	1/2 "

### Conductor Related

Conductor Range	0.17-0.45 in (4.3-11.4 mm)
Number of Conductors	Single

### Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	IP66
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	50
Pallet Quantity	10800

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - SEC50GA](#)  
[Warranty - Industrial & Commercial Products](#)