

Kellems Wire Management, Cord Connectors, European Style, .45-.71", 3/4", Gray

By Hubbell Wiring Device-Kellems

Catalog # [SEC75GA](#)

Kellems Wire Management, Cord Connectors, European Style, .45-.71", 3/4", Gray



General

Application	Straight Male Connector
Catalog Number	SEC75GA
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Low Profile Cord Connectors
Material	Non-Metallic
Material - Mounting Hardware	Locknut or Tapped Opening
Performance	Environmental - Flammability - UL 94V-2 Environmental - Operating Temperatures - -22°F to 225°F (-30°C to 107°C) Environmental - Protection Class - IP66 Suitability
Series	Low Profile NPT
Temperature Rating	Minimum -22 Deg F to 225 Deg F (-30 Deg C to 107 Deg C)
Type	Connector
UPC	783585018140

Dimensions

Display Size	3/4" NPT
Hub Size	3/4"

Conductor Related

Conductor Range	0.45-0.71 in (11.4-18.0 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	IP66
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	50
Pallet Quantity	10800

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-SEC75GA-SPEC-EN | REV 6/2024