

## Kellems Wire Management, Cord Connectors, European Style, .23-.53", PG16, Black

By Hubbell Wiring Device-Kellems  
Catalog # [SECP16BA](#)



Kellems Wire Management, Cord Connectors, European Style, .23-.53", PG16, Black

### Application

Straight Male Connector

### Performance

- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperatures - -22°F to 225°F (-30°C to 107°C)
- Environmental - Protection Class - IP66 Suitability

### General

Catalog Number	SECP16BA
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Low Profile Cord Connectors
Material	Non-Metallic
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Low Profile PG
Specifications	<ul style="list-style-type: none"><li>• Body - Nylon</li><li>• Cord Diameter Inches (mm) - .23"-.53" (5.8-13.5)</li><li>• Gland - Buna N</li><li>• Hub Size - PG16</li></ul>

Temperature Rating

Minimum -22 Deg F to 225 Deg F (-30 Deg C to 107 Deg C)

Type  
UPC

Connector  
783585018348

### Dimensions

Display Size PG16  
Hub Size PG16

### Conductor Related

Conductor Range 0.23-0.53 in (5.8-13.5 mm)  
Number of Conductors Single

### Certifications And Compliance

Industry Standard(s) UL Listed  
Nema Rating IP66

### Logistics

Carton Quantity 50

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - SECP16BA](#)  
[Warranty - Industrial & Commercial Products](#)